


Technical Datasheet



HSA

DIN rail adaptor

Description

The DIN rail adaptors of the series HSA are for mounting units with panel mount housings on a DIN rail.
When using the adaptors, enough place is left between the housing and the DIN rail for the connecting cables.

Operation

The complete set consists of 2 adaptors, 4 screws M2x12, 8 washers M2 and eventually 2 additional holders.
Turn the panel mount housing upside down and remove the 2 screws on one side of the back panel.
Fix 1 adaptor with 2 screws M2x12 and 4 washers (each 2 above and below the adaptor) to the housing.
Connect the second adaptor the same way.
Connect the cables and clip the adaptors on the DIN rail.

Ordering Information

HSA 72	For FAS 100
HSA 96	For TCE 8000 (panel housing)



Küppers Elektromechanik GmbH

www.kem-kueppers.com

info@kem-kueppers.com

KEM Headquarters

Liebigstraße 5
85757 Karlsfeld
Germany

T. +49 8131 59391-0
F. +49 8131 92604

info@kem-kueppers.com

KEM Manufacturing Center

Wetzeller Straße 22
93444 Bad Kötzing
Germany

T. +49 9941 9423-0
F. +49 9941 9423-23

production@kem-kueppers.com

KEM Sales

Liebigstraße 5
85757 Karlsfeld
Germany

T. +49 8131 59391-100
F. +49 8131 92604

sales@kem-kueppers.com

KEM Service & Repairs

Wetzeller Straße 22
93444 Bad Kötzing
Germany

T. +49 9941 9423-37
F. +49 9941 9423-24

service@kem-kueppers.com

*More distributors & partners can be found at:
www.kem-kueppers.com*